







P. C. B 设计参考尺寸




规格:

1. 额定值: DC30V 2A
2. 接触电阻: $\leq 30m\Omega$
3. 绝缘电阻: $\geq 100M\Omega$
4. 耐电压: 500VAC
5. 插拔力: 3N~30N
6. 使用寿命: 5000次
7. 使用温度: $-20^{\circ}\text{C} \sim +80^{\circ}\text{C}$



电路示意图



推荐插头尺寸

电话: 0769-82310511-867
 邮箱: hooya89@hooya.hk
 V: hooya89

					TOLERANCE UNLESS SPECIFIED						
6	COVER	PBT(UL94V-0)	1	BLACK	UP TO 5mm:±0.1	ANGULAR	A0	2022.7.18	初次发行		WM
5	CASE	PBT(UL94V-0)	1	BLACK	ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS		BY APPD
4	PLAIN FILM	BRASS	1	COPPER TIN-PLATED	TITLE: DC JACK			UNIT : MM	ROHS	DWN	
3	BENT SHEET	BRASS	1	COPPER TIN-PLATED	MODEL: DC-005FA-3.0-PU			SCALE: 1:1	COMPLIANT	CHK'D	
2	SPRING	PHOSPHOR BRONZE	1	COPPER TIN-PLATED	 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司				APPD		
1	CONTACT PIN	BRASS	1	COPPER TIN-PLATED					PRO.AGL:  		REV :A0
NO.	PART NAME	MATERIAL	QTY	FINISHING							