




SPECIFICATION  
MATERIAL & FINISHES  
INSULATOR: PBT GLASS FILLED UL94V-0  
CONTACT: BRASS  
SHELL : STEEL  
PLATING : CONTACT GOLD FLASH PLATED

ELECTRICAL  
Operation voltage: 250 VAC max.  
Current rating: 3 Amps max.  
Contact resistance: 15 mohms max.  
Insulation resistance: 3000 Mohms min @ 500 VDC  
Dielectric withstanding voltage: 1000 VAC / minute  
Operating temperature: -55°C TO +105°C



|                 |       |           |            |                                                    |                 |       |      |
|-----------------|-------|-----------|------------|----------------------------------------------------|-----------------|-------|------|
| TOLERANCE TABLE |       | APPROVED: | DATE:      | Ckmtw 深圳市灿科盟实业有限公司<br>CHANKLEMENT INDUSTRYCO., LTD |                 |       |      |
| .0              | ±0.30 | CHECKED:  | DATE:      |                                                    |                 |       |      |
| .00             | ±0.20 | DRAWN:    | DATE:      | DMS-15P 二排 公头 直插 车针 铆合锁螺丝                          |                 |       |      |
| .000            | ±0.05 | L.YF      | 2018-04-07 | CLIENT P/N                                         | D-DMSC15PM-F001 | UNIT  | mm   |
|                 |       |           |            | FILE NO.                                           | Ckmtw-DMSC-0002 | SCALE | free |
|                 |       |           |            | REV.                                               | A               | Q100  |      |