





SPECIFICATION
MATERIAL & FINISHES
 INSULATOR: PBT GLASS FILLED UL94V-0
 CONTACT: BRASS
 SHELL : STEEL
 PLATING : CONTACT GOLD FLASH PLATED

ELECTRICAL
 Operation voltage: 250 VAC max.
 Current rating: 3 Amps max.
 Contact resistance: 15 mohms max.
 Insulation resistance: 3000 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 1000 VAC / minute
 Operating temperature: -55°C TO +105°C



TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:				
DRAWN:	DATE:	PART. NO.	D-DBC015PM-A001		
L.Y.F	2018-04-07	UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DBC-0002	REV.	A

TITLE:
 DBC-15P 二排 公头 焊线式 车针 全金光孔