




材料及电镀

- ①. 螺 丝：M2.0，钢，镀锌，一字槽
- ②. 塑件主体：PA66
- ③. 夹 子：磷青铜，镀镍
- ④. 方 盒：黄铜，镀镍
- ⑤. 塑件盖板：PA66

电气性能

额定电压：300V 250V
额定电流：8A 7A
接触电阻：20mΩ (Max)
绝缘电阻：500MΩ\DC500V
耐 电 压：AC1500V\1Min
使用线径：28-16AWG 0.5-1.5mm²

机械性能

温度范围：-40℃ ~ +105℃
瞬时温度：+250℃ 5秒
扭 力：0.2N.m(2.04kgf.cm)
剥线长度：6-7mm

2	方盒	铜	镀镍	
1	基座	PA66	绿色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE		接线端子																			
料 号 PART NO		HC-JXDZK-3. 5-13P																			
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1																		
<table><tr><th colspan="3">公差参数</th></tr><tr><th>Poles</th><th>Dim</th><th>Dim</th></tr><tr><td>2-6P</td><td>±0.10</td><td>±0.20</td></tr><tr><td>7-12P</td><td>±0.20</td><td>±0.30</td></tr><tr><td>13-18P</td><td>±0.25</td><td>±0.40</td></tr><tr><td>19-24P</td><td>±0.30</td><td>±0.50</td></tr></table>		公差参数			Poles	Dim	Dim	2-6P	±0.10	±0.20	7-12P	±0.20	±0.30	13-18P	±0.25	±0.40	19-24P	±0.30	±0.50	单 位 UNIT	MM
公差参数																					
Poles	Dim	Dim																			
2-6P	±0.10	±0.20																			
7-12P	±0.20	±0.30																			
13-18P	±0.25	±0.40																			
19-24P	±0.30	±0.50																			
<table><tr><td>X.xxx</td><td>±0.10</td></tr><tr><td>X.xx</td><td>±0.30</td></tr><tr><td>X.x</td><td>±0.50</td></tr><tr><td>X.xx*</td><td>±1*</td></tr><tr><td>X.x*</td><td>±3*</td></tr><tr><td>X.*</td><td>±5*</td></tr></table>		X.xxx	±0.10	X.xx	±0.30	X.x	±0.50	X.xx*	±1*	X.x*	±3*	X.*	±5*	张 数 PART NO	1 OF 1						
X.xxx	±0.10																				
X.xx	±0.30																				
X.x	±0.50																				
X.xx*	±1*																				
X.x*	±3*																				
X.*	±5*																				
		版 本 REV	A																		
		制 图 DRAW	AhYe																		
		审 核 CHECKED	夏操云																		
		批 准 APPROVE	赵亮亮																		

