

F243-12 05 A0 C SF C 2

NQ OF PINS PER ROW	Contact	Plating	+INSULATOR	PACKING
2-50P	Full Gld	Semi-gold	MATERIAL:	A: PE Bag
	A0=0.8u"	B0=0.8U	B: PA6T	B: Tape & Reel
	A1=1u"	B1=1U	C: PA9T	C: Tube
	A2=1.5u"	B2=1.5U	D: LCP	D: Tube+CAP
	A3=2u"	B3=2U		E: Tray
	A4=3u"	B4=3U		
	A5=5u"	B5=5U		
	A6=10u"	B6=10U		
	A7=15u"	B7=15U		
	A8=20u"	B8=20U		
	A9=30u"	B9=30U		
	\$1=Q dinary Tinned			
	\$2=Matte Tinned			
	\$3=Tinned at High temperature			

Technical drawing of a 2x5 array of square pins. The top view shows a grid of 10 pins arranged in 2 rows and 5 columns. The overall width is 10.40 ± 0.25 (①*). The distance between the centers of the first and fourth pins in the top row is 8.00 ± 0.20 (②). The height of the array is 4.00 (③). The pins are numbered 1 through 5 in the first row and 2 through 6 in the second row. The side view shows the pins are square with a width of (0.38) and a height of 4.30 (④). The distance between the centers of the first and fourth pins in the side view is (2.00) . The bottom view shows the pins are square with a width of 0.50×0.2 and a height of 2.00 (⑤). The distance between the centers of the first and fourth pins in the bottom view is 2.00 (⑥*).

Recommended P. C. B. LAYOUT

General Tolerance ± 0.05

注 意 事 项

1. 带序号为必检尺寸
2. 带*为重点检验尺寸
3. 保持力为 0.4kg Min

				OPERATION		SCALE		Fillet	Yxcon 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM			
				X.XX	±0.20	SIZE	A4	DESIGN	伍思远2023.09.18	PART NO	F243-1205A0CSFC2
				X.XXX	±0.10						
A0	2023.09.18	/	新版发行	Angle	±3°	SHEET	1/1	CHECK		TITLE	2.0封口排母H=4.3 2*5P 180度 DIP:2.8 塑宽=4.0 PA9T料 镀普金
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.	