




NOTES:

- 1.Rating:12VDC 50mA
- 1.额定值: 12VDC 50mA
- 2.Dielectric Strength:100V AC
- 2.耐电压: 100V AC
- 3.Contact Resistance:≤100mΩ Max
- 3.接触电阻: ≤100mΩ
- 4.Insulation Resistance:≥100MΩ
- 4.绝缘电阻: ≥100MΩ
- 5.Operating Force:200±100gf
- 5.操作力: 200±100gf
- 6.Life: 10,000 times
- 6.寿命: 10,000 times
- 7.operate temperature:-10℃~60℃
- 7.操作温度: -10℃~60℃
- 8.Material Properties: SGS
- 8.材料属性: 环保



4	Cover 盖子	SUS	1	Silvery white 银白色
3	Contact spring 接触簧片	Bronze	2	Silvery white 银白色
2	Key 按键	Nylon	1	Black 黑色
1	Base 底座	PPA-Brass	1	Ag plating-Black 镀银-黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4					 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3						X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP609120330
A2						X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				