







N=PIN数



P. C. B LAYOUT

材料Material

原料Insulator:PBT/PA9T(UL 94V-0)

相关材料Related Material: Brass

表面涂层Surface Coating: Au Over Ni

规格Specification

额定电流Current rating:2.5AMP

耐压Dielectric Withstanding Voltage:1000v Ac Min

绝缘电阻Insulation Resistance:1000M Ω min

接触电阻Contact resistance:20M Ω Max

工作温度Working Temperature:-40℃~+105℃

Max.Processing Temp瞬时温度:

PBT 230° ±5° 10S

PA9T 260° ±5° 10S

上海洲日电子有限公司

Shanghai Zhouri Electronics CO.,LTD

上海康司玛电子科技有限公司

Shanghai Consma Electronic Technology Co., Ltd

tel:021-51571121

fax:021-51571120

<http://www.zhouri.net>

<http://www.ksmchina.com>

产品名称:

PM 2.54-1*N H5.7

绘图:

牛万龙

日期:20250626

审核:

张海娜

日期:20250626

版本编号:

ZRLCGY2025-06-26-CJ A/2

第三视角:



单位: mm

比例:

图幅:A4

页次 共 01 第 01