




SPECIFICATION

MATERIAL & FINISHES

INSULATOR: PBT GLASS FILLED UL94V-0

CONTACT: BRASS

SHELL : STEEL

PLATING : CONTACT GOLD FLASH PLATED

ELECTRICAL

Operation voltage: 250 VAC max.



Current rating: 3 Amps max.

Contact resistance: 15 mohms max.

Insulation resistance: 3000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1000 VAC / minute

Operating temperature: -55°C TO +105°C



TOLERANCE TABLE

.0 ± 0.30

.00 ± 0.20

.000 ± 0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: DBC-25P 公头 焊线式 车针 全金光孔			
DRAWN: LYF	DATE: 2018-04-07	PART. NO.	D-DBC025PM-A001		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DBC-0003		REV. A