



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.07.29	阿树




Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:3A AC/DC
额定电流: 3A AC/DC
Withstanding voltage:1000V
AC/minute
耐受电压: 1000V AC/分钟
Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤20mΩ
接触电阻: ≤20mΩ

PART NO.:

X2081 H-2xXX-N0
① ② ③ ④

- ①Series No
②Category:H-Housing
③Row No-Pin No:2xXX-2x05P~2x20P
④Material:N0-PA66 94V-0



Poles	Dimension(mm)			Poles	Dimension(mm)		
	A	B	C		A	B	C
2x05	12.00	8.00	10.60	2x13	28.00	24.00	26.60
2x06	14.00	10.00	12.60	2x14	30.00	26.00	28.60
2x07	16.00	12.00	14.60	2x15	32.00	28.00	30.60
2x08	18.00	14.00	16.60	2x16	34.00	30.00	32.60
2x09	20.00	16.00	18.60	2x17	36.00	32.00	34.60
2x10	22.00	18.00	20.60	2x18	38.00	34.00	36.60
2x11	24.00	20.00	22.60	2x19	40.00	36.00	38.60
2x12	26.00	22.00	24.60	2x20	42.00	38.00	40.60

X2081H-2xXX-N0	PA66 UL 94V-0	AWG#28-22	X2081W	X2081T
PART NO	Material	Wire Range	Suitable XKB Wafer	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	2.0mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X2081H-2xXX-N0
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1