







REV.	ECN NO.	REVISED	DATE



PCB Layout Diagram
Top View




工程部
2022-04-26
LQ. HUANG

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	Huanglieqing	DATE	2022-04-26
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2022-04-26
X.X :±0.25	X.X :±0.5°	APVD	XueShunyong	DATE	2022-04-26
X.XX :±0.20		SCALE: 2:1	SIZE: A4	VIEW:	
X.XXX :±0.10		UNIT: mm	REV.: A/0	OBJECT: MY	
WEIGHT: 0.60g					
SHEET 1 OF 2					
TITLE:		电池扣CR2032-P SMT 卷装			
PART NO.:		MY-2032-08-R			
DRAW NO.:		MY-CP-0154			







1	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.25mm	Ni-Plating
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR



产品





标签朝上



出料方向



余留封带长: 280 MIN
载带与封带剥离
剥离角度: 165° -180°
剥离强度: 0.1-1.0N



Detail A

技术要求:

1. 圆孔十个孔距距离累计允许公差为 $\pm 0.2\text{mm}$
2. 带长250mm内容许弯曲度1mm
3. 材料厚度以在载带边缘测量为准
4. 所有尺寸定义依循EIA-481-C系准则定义之
5. 材料: 黑色PS T=0.35mm
6. 所有卷轮为灰蓝挖空旋转塑胶卷轮
7. 整模成型长度: 12.576M,
8. 非指明公差范围为: $\pm 0.1\text{mm}$; 超过250mm不计算累计误差
9. 型腔外形凡未标明处倒角R为0.2-0.3; 拔模斜度未标注的为 3° 以下

包装信息:

- 1、每卷盘装产品 500 只, 卷盘外侧贴相关标签;
- 2、每 6 卷盘放在一个塑料袋中;
- 3、每外箱装6盘, 产品总数: 3000 只;
- 4、外箱上下用胶纸封成“工”字;
- 5、电池扣包材CR2032-P SMT 卷装44MM(MY-2032-P-01-R)

工程部
2023-11-15
H. WANG

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	WangHeng	DATE	2023-11-15
X : ±***	X : ±***	CHKD	ZhouRuicai	DATE	2023-11-15
X.X : ±***	X.X : ±***	APVD	XueShunYong	DATE	2023-11-15
X.XX : ±***	X.XX : ±***	WEIGHT:	SCALE:	SIZE: A4	VIEW:
X.XXX : ±***	X.XXX : ±***	SHEET 2 OF 2	UNIT: mm	REV.: A/0	OBJECT: MY
				TITLE: 电池扣CR2032-P SMT 卷装	
				PART NO.: MY-2032-08-R	
				DRAW NO.: MY-BD-0002	