







PCB.焊接图  
PCB.WELDING DRAWING



NOTES:

- 1.Rating:12VDC 50mA  
1.额定值: 12VDC 50mA
- 2.Dielectric Strength:250V AC  
2.耐电压: 250V AC
- 3.Contact Resistance:≤100mΩ Max  
3.接触电阻: ≤100mΩ
- 4.Insulation Resistance:≥100MΩ  
4.绝缘电阻: ≥100MΩ
- 5.Operating Force:160±50gf  
5.操作力: 160±50gf
- 6.Life: 20,000 times  
6.寿命: 20,000 times
- 7.Travel: 0.20±0.01mm  
7.行程: 0.20±0.01mm
- 8.Operation temperature:-20℃~+80℃  
8.工作温度: -20℃~+80℃



| 5        | Button<br>按钮      | PPA            | 1         | white<br>白色               |
|----------|-------------------|----------------|-----------|---------------------------|
| 4        | Cover plate<br>盖板 | SUS            | 1         | Copper tin plating<br>镀铜锡 |
| 3        | Shrapnel<br>弹片    | SUS            | 1         | Ag plating<br>镀银          |
| 2        | Body<br>本体        | PPA            | 1         | white<br>白色               |
| 1        | Card<br>卡件        | Brass          | 1         | Ag plating<br>镀银          |
| NO<br>序号 | Part name<br>部件名  | Material<br>材料 | QTY<br>数量 | Remark<br>备注              |

| A4  |      |          |             |       |
|-----|------|----------|-------------|-------|
| A3  |      |          |             |       |
| A2  |      |          |             |       |
| A1  |      |          |             |       |
| REV | DATE | REVISION | DESCRIPTION | ISSUE |



COMMON TOLERANCE

|         |        |
|---------|--------|
| X.XX    | ± 0.10 |
| X.X     | ± 0.15 |
| X       | ± 0.25 |
| ANGULAR | —      |

| UNIT                                                                                                                                                      | MM     | PROJECTED  | PRODUCT NAME: |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------|--------|------------|---------------|
| DRAWN BY                                                                                                                                                  | FUYUAN | CHECKED BY | COCO          |
| DATE                                                                                                                                                      | 2019   | APPROVAL B | ALEN          |
| MODEL NO: TP14721650                                                                                                                                      |        |            |               |
| Https: www.rocpcu.tw                                                                                                                                      |        |            |               |
| ROPCU TECHNOLOGY CO.,LTD                                                                                                                                  |        |            |               |
| Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission |        |            |               |