





电话：0769-82310511-867  
邮箱：hooya89@hooya.hk  
V：hooya89



P.C.B LAYOUT  
BOTTOM VIEW

H=3mm

|     |              |                       |     |           | TOLERANCE<br>UNLESS SPECIFIED                                                                                                             |         |            |           |                                                                                                                                                                                              |         |
|-----|--------------|-----------------------|-----|-----------|-------------------------------------------------------------------------------------------------------------------------------------------|---------|------------|-----------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|
| 7   |              |                       |     |           | UP TO 5mm: ±0.1                                                                                                                           | ANGULAR | 1          |           |                                                                                                                                                                                              |         |
| 6   | SPRING PLATE | PHOSPHOR BRONZE STRIP | 1   | NATURAL   | ABOVE 5mm: ±0.2                                                                                                                           | ±1°     | NO         | DATE      | REVISIONS                                                                                                                                                                                    | BY APPD |
| 5   | CONTACT CLIP | PHOSPHOR BRONZE       | 1   | Ag CLAD   | TITLE: VERTICAL SLIDE SWITCH                                                                                                              |         | UNIT : MM  | ROHS      | DWN                                                                                                                                                                                          |         |
| 4   | TERMINAL     | BRASS STRIP           | 3   | Ag PLATED | MODEL: SS-12E29G3-001                                                                                                                     |         | SCALE: 1:1 | COMPLIANT | CHK'D                                                                                                                                                                                        |         |
| 3   | BASE         | PHENOLIC RESIN        | 1   | NATURAL   |  DONGGUANG HAOYU ELECTRONICS CO., LTD<br>东莞市弘皓电子有限公司 |         | APPD       |           | PRO.AGL:   REV :A0 |         |
| 2   | FRAME        | STEEL STRIP           | 1   | Ni PLATED |                                                                                                                                           |         |            |           |                                                                                                                                                                                              |         |
| 1   | KNOB         | PA66                  | 1   | BLACK     |                                                                                                                                           |         |            |           |                                                                                                                                                                                              |         |
| NO. | PART NAME    | MATERIAL              | QTY | FINISHING |                                                                                                                                           |         |            |           |                                                                                                                                                                                              |         |