

焊脚尺寸以顺畅过孔规为准

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES





- MATERIAL

 - HOUSING MATERIAL: LCP BLACK UL94V-0.
 - CONTACT MATERIAL: PHOSPHOR BRONZE T=0.25mm.
 - PLATING: GOLD AND TIN PLATING OVER NICKEL.
 - SHIELD: BRASS WITH NICKEL PLATED.
- ELECTRICAL


 - VOLTAGE RATING: 125 VAC RMS.
 - CURRENT RATING: 1.5 AMP.
 - CONTACT RESISTANCE: 40 MILLIOHMS MAX.
 - INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC.
 - DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.
- MECHANICAL

 - DURRABILITY: 750 CYCLES MIN.
 - MATING/UNMATING FORC: 2.24 KG.F MAX.
- ENVIRONMENTAL:


 - STORAGE: -40~+85.
 - OPERATION: -40~+85.




8	—
7	—
6	RX-
5	—
4	—
3	RX+
2	TX-
1	TX+
PIN	说明



PCBLAOUT T=1.2
TOL:±0.05



壳子脚



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.:±0.35	X':±3"	PART NO. RJ45-4001-8P	TITLE: RJ45 9.9H 流板5.8 有壳无灯DIP	
X.X:±0.25	X.X':±2"		DESIGN: Ethan	
X.XX:±0.15	X.XX':±1"	CHED: Olvia		MANUFACTURE DWG
UNITS	mm	APPD: Ava		SCALE N:A
MATERILA	— — —			SHEET 1/1
FINISH	— — —			