



SPECIFICATION
MATERIAL & FINISHES
INSULATOR: PBT GLASS FILLED UL94V-0
CONTACT: BRASS
SHELL : STEEL
PLATING : CONTACT GOLD FLASH PLATED

ELECTRICAL
Operation voltage: 250 VAC max.
Current rating: 3 Amps max.
Contact resistance: 15 mohms max.
Insulation resistance: 3000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 1000 VAC / minute
Operating temperature: -55°C TO +105°C

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:				
DRAWN:	DATE:	PART. NO.	D-DBC015PF-A001	UNIT	mm
LXF	2018-04-07	FILE NO.	Ckmtw-DBC-0007	SCALE	free
				REV.	A