


REV		REVISIONS			DWN	CHK	DATE
NUMBER	DESCRIPTION						
A	DESIGN						

Kinghelm®



NOTES:

- ELECTRICAL:
 - VOLTAGE RATING:DCV 300V 10MS
 - CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - INSULATION RESISTANCE: 5.0M OHM/MIN.
 - THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES
- MATERIAL:
 - SEE TABLE
- ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
			AS
②	接头	1代 IPEX端子	1
①	同轴线	RF1.37黑线,OD:1.37mm	AS

深圳市金航标电子有限公司

www.kinghelm.com.cn

KHA-(RG1.37)-TX120-IPEX-221

0755-28190160

ALL DIMENSION
ARE IN MM

DRAWN Jamy

DATE 2020-06-15

ENG.


COMPUTER GENERATED
IN SOLIDWORKS

MFG.

DO NOT SCALE
THIS DRAWING

Q.A.

PROJECTION



GENERAL TOLERANCE FOR
ANGLES X.X X.XX X.XXX
± 1° ± 0.3 ± 0.25 ± 0.150

SIZE Number

B

REV

A

CUSTOMER PIN:

SCALE: Free

TYPE

SHEET 1 OF 1