

RoHS&REACH

REV.	ECN NO.	DESCRIPTION	REVISED	DATE
				2021.2.4

NOTES:

MATERIAL:

1. HOUSING MATERIAL :ABS (UL94-0); BLACK;
2. CONTACT MATERIAL :ROUND PINS-0.46mm DIAMETER PHOSPHOR BRONZE; GOLD PLATING OVER NICKEL; Fu"; :UL 1061 26 AWG,200MM;


3. WIRES

ELECTRICAL/PHYSICAL:

1. VOLTAGE RATING :125 VAC RMS
2. CURRENT RATING :1.5 AMP
3. CONTACT RESISTANCE :30 MILLIOHMS MAX2
4. INSULATION RESISTANCE :500 MEGOHMS MIN @500V DC
5. DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 60Hz. 1MIN
6. DURABILITY :750 CYCLES MIN
7. TEMPERATURE :-40°C/+85°C

648K - X X - X X X L: Wire Length

Positions	Contacts	Wire Style	Color	Gold Plating
8 or 10	2~10	1-24 AWG 2-26 AWG 3-28 AWG	1-Black 2-Gray 3-Other	1-G/Fu" 2-3u" 3-6u" 4-15u" 5-30u" 6-50u"



10	-	-
9	白	200mm
8	棕	200mm
7	蓝	200mm
6	橙	200mm
5	绿	200mm

4	黄	200mm	4	反端	8	黄铜
3	红	200mm	3	金线	8	磷铜 Fu"
2	黑	200mm	2	电子线	8	UL1061 26AWG
1	-	-	1	648K塑壳	1	ABS 黑色阻燃
线序	648K	长度	序号	物料名称	数量	材质

除非另行说明，否则公差按照下表	设计	RD	比例	1: 1
尺寸标注	公差	审核	单位	mm
.X	±0.25 ±2.0°	批准	图幅	A4
.XX	±0.20 ±1.5°	角法	版本	A-0
.XXX	±0.15 ±1.0°		图数	第1页 共1页
	±0.10 ±0.5°		产品型号	648K 10P8C ABS黑色 L=200 Fu"
			产品编号	265001-44

设计	RD	比例	1: 1
审核		单位	mm
批准		图幅	A4
角法		版本	A-0
		图数	第1页 共1页

 恒连电子科技有限公司			
EVERCOM ELECTRONIC TECHNOLOGY CO., LTD			
http://www.chinarj45.com			
产品型号	648K 10P8C ABS 黑色 L=200 Fu"		
产品编号	265001-44		
	图	纸	编 号