

Ordering Information

备注(Remark)

1. 材料(MATERIAL)

胶芯: PBT+30%G. F UL94V-0, 颜色: 黑色.

Housing:PBT+30%G. F UL94V-0, Color:Black

四方针：黄铜，镍底30u"MIN, 表面镀金3u"MIN

Contact: Brass, 3u" MIN GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Raring Current:3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.





Insulating Resistance:1

耐电压: AC 500V/分钟.

Withstanding Voltage:

温度范围: -40°C to $+105^{\circ}\text{C}$

Temperature Range: -40°C to $+125^{\circ}\text{C}$



RoHS
COMPLIANT

注意事项

1. 带*为品质重点检验尺寸

				OPERATION		SCALE		Fit		 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.	
				X.X	±0.25	UNIT		MM			
				X.XX	±0.20	SIZE	A4	DESIGN	李官淼2021.12.16	PART NO.	P125-1108A4AS116A1
				X.XXX	±0.10						
A0	2021.12.16	/	新版发行	Angle	±3°	SHEET	1/1	CHECK		TITLE	2.54排针 1*8P L=11.6/3.0 180度 PBT 镀3U金 500/袋
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.	