



NOTE:
Rating: DC 12V 0.1A
Operating Force: ≤31gf
Lifetime: 50,000 Cycles

⑤	Contact Spring	—	1	Phosphor bronze	Ag Plated	_____
④	Terminal	—	4	Brass	Ag Plated	_____
③	Housing	—	1	PA	Black	_____
②	Cover	—	1	PA	Black	_____
①	Slider	—	1	PA	White	_____
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS				DATE	hro®	
DRAWN	LIUCAN	2022.5.16				
CHECKED			TITLE: DETECTOR SWITCHS			
APPROVALS			PART NO. K5-1631DA-02			
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20		PROJ:	
		5~10	±0.15	±2°	DRAWING NO.	
		~ 5	±0.10		SHEET	1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.