




NOTES:

- 1.Rating:12VDC 50mA
- 1.额定值: 12VDC 50mA
- 2.Dielectric Strength:100V AC
- 2.耐电压: 100V AC
- 3.Contact Resistance:≤100mΩ Max
- 3.接触电阻: ≤100mΩ
- 4.Insulation Resistance:≥100MΩ
- 4.绝缘电阻: ≥100MΩ
- 5.Operating Force:200±100gf
- 5.操作力: 200±100gf
- 6.Life: 10,000 times
- 6.寿命: 10,000 times
- 7.operate temperature:-10℃~60℃
- 7.操作温度: -10℃~60℃
- 8.Material Properties: SGS
- 8.材料属性: 环保



4	Cover 盖子	SUS	1	Silvery white 银白色
3	Contact spring 接触簧片	Bronze	2	Silvery white 银白色
2	Key 按键	Nylon	1	Black 黑色
1	Base 底座	PPA-Brass	1	Ag plating-Black 镀银-黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4					 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3						X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP609120340
A2						X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				