




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2020.11.10	钟建虾
02	△	刪除多餘視圖	2021.03.19	钟建虾



模穴號1.2.3...




(打正 "K" )

### Specifications:

Current rating: 2A AC/DC.  
Voltage rating: 100V AC/DC  
Temperature range: -40°C ~ +105°C.  
Contact resistance: 20mΩ Max.  
Insulation resistance: 1000MΩ Min.  
Withstanding voltage: 800V AC/minute  
Material: PA9T.UL94V-0.

All materials must meet GREENCONN hazardous substances control standards.



Recommended P.C.B Layout(Top Side)  
P.C.B Thickness=1.20mm (Tolerance=±0.05)

### Ordering Information

G WFA102 - 03 XX A 803 D X B X - 9B

No. of Pins per Row 03 Standard Plating  
01=Tin Selective Plating  
22=Matte Tin

Color  
1=Black  
2=White Standard Packing  
F=CAP+Tape&Reel  
Selective Packing  
C=Tube  
N=PE Bag