





Ordering Information

30u" MIN NICKEL UNDERPLATING OVER ALL

Temperature Range: -40°C to $+105^{\circ}\text{C}$



NG
Bag
be & Reel

be
be+CAP
ay

S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High-temperature

1. 带*为品质重点检验尺寸

				OPERATION		SCALE		Fit	 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.		
				X.X	±0.25	UNIT		MM	www.yxcon.com		
				X.XX	±0.20	SIZE	A4	DESIGN	刘伟 2021.05.10	PART NO	F343-1114A0CSUC1
				X.XXX	±0.10						
A0	2021.05.10	/	新版发行	Angle	±3°	SHEET	1/1	CHECK		TITLE	1.27排母 4.3mm塑高 1*14P 180度 DIP:2.4 U型 PA9T料 镀普金 33/管装
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.	