








NOTES:

1. Rating: 12VDC 50mA
1. 额定值: 12VDC 50mA
2. Dielectric Strength: 100V AC
2. 耐电压: 100V AC
3. Contact Resistance: ≤ 100mΩ Max
3. 接触电阻: ≤ 100mΩ
4. Insulation Resistance: ≥ 100MΩ
4. 绝缘电阻: ≥ 100MΩ
5. Operating Force: 200 ± 50gf
5. 操作力: 260 ± 50gf
6. Life: 10,000 times
6. 寿命: 10,000 times
7. Operating Temperature: -10°C to +60°C
7. 使用温度: -10 to +60°C



5	Terminal 端子	Brass	1	Ag plating 镀银
4	外壳	SUS	1	
3	簧片	Silver copper 复银铜	2	Ag plating 镀银
2	按柄	PA46	1	Black 黑色
1	Pedestal 基座	PPA	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL B	ALEN
MODEL NO: TP611120230			
Https: www.rocpcu.tw			
ROPCU TECHNOLOGY CO.,LTD			
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			