

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		图面升级整理图面	2024.08.15	阿 树

- SPECIFICATIONS
- Voltage rating:250V AC/DC
 - Current rating:7A AC/DC
 - Withstanding Voltage:1500V AC/minute
 - Temperature range:−45°C~+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤10mΩ
 - After environmental testing:≤20mΩ
 - Material:过灼热丝850°C

PART NO.:
X9636 H-XX-N0-U
① ② ③ ④ ⑤

- ① Series No
② Category:H-HSG
③ Row No-Pin No: XX-02P~15P
④ Material:N0-PA66 94V-0
⑤ Social No:U-upgaded version

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	3.96	8.02	09	31.68	35.74
03	7.92	11.98	10	35.64	39.70
04	11.88	15.94	11	39.60	43.66
05	15.84	19.90	12	43.56	47.62
06	19.80	23.86	13	47.52	51.58
07	23.76	27.82	14	51.48	55.54
08	27.72	31.78	15	55.44	59.50

X9396H-XX-N0-U	PA66	X9396W	X9396T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

			DESIGN	阿 树	VIEW: 	MODEL TYPE: 3.96mm Crimp Style Connectors			
X.	±0.40		CHECKED		UNIT: mm/in	PART NO.: X9396H-XX-N0-U			
X.x	±0.30								
*X.xx	±0.20								
X.xxx	±0.15		APPROVED		SIZE: A4	DWG NO.:			
UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED					SCALE	PAGE	REVISION
Jg.cn							N/A	1/1	A1