







PARTS DIMENSION TABLE

parts no.	DIM. a	DIM. b	inner thread
B/C	4.8	11.8	4#40
D/E	5.8	12.0	4#40

SPECIFICATION
MATERIAL & FINISHES
INSULATOR: PBT GLASS FILLED UL94V-0
CONTACT: BRASS
SHELL : STEEL
PLATING : CONTACT GOLD FLASH PLATED

ELECTRICAL
Operation voltage: 250 VAC max.
Current rating: 3 Amps max.
Contact resistance: 15 mohms max.
Insulation resistance: 3000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 1000 VAC / minute
Operating temperature: -55°C TO +105°C



RECOMMENDED P.C.B LAYOUT (TOP VIEW)
TOLERANCES: ±0.10mm

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:				
DRAWN:	DATE:	DMRC-25P 公头 弯插 车针 铆合锁螺丝 全金 折弯7.2 带黑胶挡板			
L.Y.F	2018-04-07				
PART. NO.		D-DMRC25PM-E001			
UNIT	mm	SCALE	free	REV.	A
FILE NO.		Ckmtw-DMRC-0004			