





Circuit diagram

NO.1	
PART NO	H
A	1.8
B	2.0

NO.3	
PART NO	MATERIAL/QTY
D	SUS/2PCS

NO.2	
PART NO	VIGOR
2	130±30
3	160±35
4	250±35

NO.4-NO.5	
PART NO	NOTE
01~99	SERIAL NUMBER



PCB Layout

⑥	Dust cover	—	1	PI	Yellow	—
⑤	Terminal	—	2	Brass	Plating silver	—
④	Contact	—	2	F.Ag/SUS	—	—
③	Base	—	1	LCP	Black	—
②	Cover	—	1	SUS	—	—
①	Keystoke	—	1	LCP	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	LIUCAN	2021.6.3					
CHECKED				TITLE:	TACT SWITCHS		
APPROVALS				PART NO.	K2-1807SM-□□□W-□□		
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
			±2'	DRAWING NO.	_____	SHEET 1 OF	

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.