





SEC:A-A



SEC:B-B



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃-+125℃

温度范围: -40℃-+125℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X2505 T - P SN
① ② ③ ④

1.Series No

2.Category:T-Terminal

3.Material:P-Phosphor Bronze

4.Plating:SN-Tin Plated

X2505T-PSN	Phosphor Bronze	AWG#26~24	X2505H
PART NO	Material	Wire Range	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connector
DWN		VIEW:	PART NO.: X2505T-PSN
CHKD		UNIT: mm/in	DWG NO.: X-X2505T-PSN
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0

ANGLAR	±5°
Δx	L ≤ 4 ±0.2
Δx	4 < L ≤ 16 ±0.3
Δx	16 < L ≤ 63 ±0.4
MARK	L > 63 ±0.5

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED