

PRODUCT NO.	1
DSHP02TJGET	RoHS compliant

NOTES :1.Specification:

1>.Operating force:1000gf Max

2>.Operating Temperature:−40° to+85°

3>.Storage Temperature:−40° to+85°

4>.Electricallife Life:2000cycles 25mA 24VDC

5>.Mechanical Life:3000cycles Operations

2. PLATING:

GOLD FLASH 1u"~2u" SOLDERTAIL,

1u"~3u"GOLD PLATING ON THE CONTACT AREA,

WITH 50u" NICKEL UNDERPLATINGOVERALL.

3. PART NUMBER DESCRIPTION :

DSHP XX T J G E T

[包装方式: T=管装 R=Reel]




[电镀层 :E= 接触部 1u"~3u" 焊脚部 1u"~2u"]

[G= 镀全金 S= 内镀金(接触部)外镀锡 (焊脚部)]



[脚型: S脚 / J脚 / H脚 / A脚 / Z脚]

[T= 低推贴胶 S= 低推不贴胶 L=长推]

[产品数 :02=2P 04=4P 08=8P 10=10P]



[Schematic]



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)

Number	Part Name	Material	Finished	TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	东莞市广督实业有限公司 DongGuan Kingtek Industrial Co., Ltd.			
①	Actuator	UL94 V0	White	LINER	ANGLES	PROJECTION	TITLE			
②	Cover	UL94 V0	Black	.0 ± 0.25	0. ± 2°		BY DSHP SERIES PITCH 1.27mm			
③	Movable	Beryllium Copper	1u"~3u" Gold	.00 ± 0.15	.0 ± 1°		PRODUCT FAMILY DSHP SERIES			
④	Terminal	Brass	1u"~2u" Gold	.000± 0.10	.00± 0.5°		PRAT NO. DSHPO2TJGET			
⑤	Base	UL94 V0	Black	DESIGN	kathy	03/20/12°	FILE NO. DSHPO2TJGET-A			
⑥	Terminal Contact	Brass	1u"~3u" Gold	DRAWING			SIZE	UNIT	SCALE	SHEET
⑦	Mylar	UL94 V0	0.05mm	CHECK			A4	mm	2 : 1	1 OF 1
				APPRO.					REV.	A