




材料及电镀

①. 螺 丝: M2.0, 钢, 镀锌, 一字槽

②. 塑件主体: PA66

③. 夹 子: 磷青铜, 镀镍

④. 方 盒: 黄铜, 镀镍

⑤. 塑件盖板: PA66

电气性能

额定电压: 300V

额定电流: 8A

接触电阻: 20mΩ (Max)

绝缘电阻: 500MΩ \ DC1000V

耐 电 压: AC1500V \ 1Min

使用线径: 24-14AWG 0.5-1.5mm²

机械性能

温度范围: -40℃ ~ +105℃

瞬时温度: +250℃ 5秒

扭 力: 0.2N.m (1.77Lb.in)

剥线长度: 6-7mm

2	方盒	铜	镀镍	
1	基座	PA66	绿色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE		接线端子																					
料 号 PART NO		HC-JXDZK-3.81-7P																					
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1																				
公差参数 <table><tr><th>Poles</th><th>Dim</th><th>DimP</th><th>DimL</th></tr><tr><td>2-6P</td><td>±0.10</td><td>±0.20</td><td></td></tr><tr><td>7-12P</td><td>±0.20</td><td>±0.30</td><td></td></tr><tr><td>13-18P</td><td>±0.25</td><td>±0.40</td><td></td></tr><tr><td>19-24P</td><td>±0.30</td><td>±0.50</td><td></td></tr></table>		Poles	Dim	DimP	DimL	2-6P	±0.10	±0.20		7-12P	±0.20	±0.30		13-18P	±0.25	±0.40		19-24P	±0.30	±0.50		单 位 UNIT	MM
Poles	Dim	DimP	DimL																				
2-6P	±0.10	±0.20																					
7-12P	±0.20	±0.30																					
13-18P	±0.25	±0.40																					
19-24P	±0.30	±0.50																					
X. X ±0.35		张 数 PART NO	1 OF 1																				
X. XX ±0.25		版 本 REV	A																				
X. XXX ±0.15		制 图 DRAW	AhYe																				
		审 核 CHECKED	夏操云																				
		批 准 APPROVE	赵亮亮																				



SECTION A-A