






PRODUCT NO.	RoHS compliant
DSHP06TSGER	



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)

Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Beryllium Copper	3μt Gold
④	Terminal	Brass	1μt Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	3μt Gold
⑦		Mylar	0.05mm

NOTES :1.Specification:

- 1>.Operating force:1000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Electrical life:1000cycles 25mA 24VDC
- 5>.Mechanical Life:3000cycles Operations

2. PLATING:



GOLD FLASH 1u”(min.) SOLDER TAIL,
3u” GOLD PLATING ON THE CONTACT AREA,
WITH 50u” NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION :

DSHP XX I S G E R

- 〔包装方式: T=管装 R=Reel〕
- 〔电镀层: B=镀锡部 3u” 焊脚部 1.2u” G=镀金部 3u” 焊脚部 3u” F=镀金部 10u” 焊脚部 10u”〕
- 〔G=镀金 S=内镀金(接触部) 外镀锡(焊脚部)〕
- 〔脚型: S脚 / J脚 / I脚 / A脚 / Z脚〕
- 〔T=低推贴胶 S=低推不贴胶 L=长推〕
- 〔产品代码: 02=2P 04=4P 06=6P 08=8P 10=10P 12=12P〕

[Schematic]



TOLERANCE UNLESS OTHERWISE SPECIFIED				INSPECTION COPY	
LINER	ANGLES			PROJECTION	
0 ± 0.25	0. ± 2°			BY DSHP SERIES PITCH 1.27mm	
.00 ± 0.15	.0 ± 1°			PRODUCT FAMILY DSHP SERIES	
.000± 0.10	.00± 0.5°			PRAT NO. DSHP06TSGER	
DESIGN				FILE NO. DSHP06TSGER-A	
DRAWING				SIZE UNIT SCALE SHEET REV.	
CHECK				A4 mm 2 : 1 10F-1 A	
APPRO.					

东莞市广智实业有限公司
Dongguan Kingtek Industrial Co., Ltd.