



P.C.B LAYOUT

材料Material

原料Insulator:PBT/PA9T(UL 94V-0)

相关材料Related Material: Brass

表面涂层Surface Coating: Au Over Ni

规格Specification

额定电流Current rating:2.5AMP

耐压Dielectric Withstanding Voltage:1000v Ac Min

绝缘电阻Insulation Resistance:1000M Ω min

接触电阻Contact resistance:20M Ω Max

工作温度Working Temperature:-40 $^{\circ}$ C~+105 $^{\circ}$ C

Max.Processing Temp瞬时温度:

PBT 230 $^{\circ}$ $\pm 5^{\circ}$ 10S

PA9T 260 $^{\circ}$ $\pm 5^{\circ}$ 10S

上海洲日电子有限公司

Shanghai Zhouri Electronics CO.,LTD

上海康司玛电子科技有限公司

Shanghai Consma Electronic Technology Co., Ltd

tel:021-51571121

<http://www.zhouri.net>

fax:021-51571120

<http://www.ksmchina.com>

产品名称:

PM 2.54-1*N

绘图: 牛万龙 日期:20250626

审核: 张海娜 日期:20250626

版本编号: ZRLCGY2025-06-26-CJ A/2

第三视角:

单位: mm

比例:

图幅:A4

页次 共 01 第 01