



N=PIN数

材料Material

原料Insulator:PBT/PA9T (UL 94V-0)

相关材料Related Material: Brass

表面涂层Surface Coating: Au Over Ni

规格Specification

额定电流Current rating:2.5AMP

耐压Dielectric Withstanding Voltage:1000v Ac Min

绝缘电阻Insulation Resistance:1000MΩ min

接触电阻Contact resistance:20MΩ Max

工作温度Working Temperature:-40℃~+105℃

Max. Processing Temp瞬时温度:

PBT 230° ±5° 10S

PA9T 260° ±5° 10S

P.C.B LAYOUT

				Shanghai Zhouri Electronics CO.,LTD			
				上海康司玛电子科技有限公司			
				Shanghai Consma Electronic Technology Co., Ltd			
绘图:	牛万龙	日期:20250626	tel:021-51571121		http://www.zhouri.net		
			fax:021-51571120		http://www.ksmchina.com		
审核:	张海娜	日期:20250626					
版本编号:	ZRLCGY2025-06-26-CJ A/2		产品名称:		PZ2. 54-2xN		
第三视角:		单位: mm	比例:		图幅: A4	页次 共 01 第 01	