





Circuit Diagram

| NO.1    |     |
|---------|-----|
| PART NO | H   |
| B       | 2.5 |
| A       | 2.7 |
| C       | 3.1 |
| D       | 3.4 |
| I       | 3.7 |
| N       | 4.0 |
| G       | 4.3 |
| P       | 4.5 |
| Q       | 4.8 |
| F       | 5.0 |
| R       | 5.2 |
| E       | 5.5 |

| NO.2    |        |
|---------|--------|
| PART NO | vigor  |
| 1       | 90±30  |
| 2       | 130±30 |
| 3       | 180±30 |
| 4       | 250±30 |
| 5       | 350±50 |

| NO.3    |              |
|---------|--------------|
| PART NO | MATERIAL/QTY |
| S       | SUS/1PC      |
| C       | C5210/1PC    |
| D       | SUS/2PCS     |
| F       | C5210/2PCS   |

| NO.4-NO.5 |               |
|-----------|---------------|
| PART NO   | NOTE          |
| 01~99     | SERIAL NUMBER |



|      |           |         |      |              |                |        |
|------|-----------|---------|------|--------------|----------------|--------|
| ⑤    | Terminal  | —       | 4    | Copper(0.3t) | Plating silver | —      |
| ④    | Contact   | —       | 1    | F.Ag/C5210   | Natural        | —      |
| ③    | Base      | —       | 1    | Nylon        | Black          | —      |
| ②    | Cover     | —       | 1    | Brass(0.15t) | Plating Nickel | —      |
| ①    | Keystoke  | —       | 1    | Nylon        | Red            | —      |
| ITEM | PART NAME | TER'NO. | QTY. | MATERIAL     | FINISHING      | REMARK |

|                |  |        |       |           |             |                                                                                       |                                                                                             |
|----------------|--|--------|-------|-----------|-------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|
| APPROVALS      |  |        |       | DATE      |             |  |                                                                                             |
| DRAWN          |  | LIUCAN |       | 2020.9.11 |             |                                                                                       |                                                                                             |
| CHECKED        |  |        |       |           |             | TITLE: TACT SWITCHS                                                                   |                                                                                             |
| APPROVALS      |  |        |       |           |             | PART NO. K2-1157SW-□□□W-□□                                                            |                                                                                             |
| TOLERANCES ARE |  | 30~以上  | ±0.30 | ANGLE     | UNIT: mm    | SCALE: 1:1                                                                            | PROJ:  |
|                |  | 10~30  | ±0.20 |           |             |                                                                                       |                                                                                             |
|                |  | 5~10   | ±0.15 |           |             |                                                                                       |                                                                                             |
|                |  | ~ 5    | ±0.10 |           |             |                                                                                       |                                                                                             |
|                |  |        |       | ±2'       | DRAWING NO. | _____                                                                                 | SHEET 1 OF 1                                                                                |

|         |      |       |              |         |        |        |
|---------|------|-------|--------------|---------|--------|--------|
| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |
|         | A    |       | NEW          |         |        |        |