

PRODUCT NO.	1	2	3	4	5	6
DSHP08TJGET	RoHS compliant					







REV.	ECN NO.	DR	DATE

NOTES :1.Specification:
1>.Operating force:1000gf Max
2>.Operating Temperature:-40° to+85°
3>.Storage Temperature::-40° to+85°
4>.Electrical life Life:2000cycles 25mA 24VDC
5>.Mechanical Life:3000cycles Operations

2. PLATING:
GOLD FLASH 1u"~2u" SOLDER TAIL,
1u"~3u" GOLD PLATING ON THE CONTACT AREA,
WITH 50u" NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION :

DSHP XX T J G E T
[包装方式: T=管装 R=Reel]
[电镀层:E=接触部1u"~3u" 焊脚部1u"~2u"]
[G=镀全金 S=内镀金(接触部)外镀锡(焊脚部)]
[脚型: S脚 / J脚 / H脚 / A脚 / Z脚]
[T=低推贴胶 S=低推不贴胶 L=长推]
[产品数: 02=2P 04=4P 08=8P 10=10P]



Number	Part Name	Material	Finished	TOLERANCE UNLESS OTHERWISE SPECIFIED				INSPECTION COPY		东莞市广督实业有限公司 DongGuan Kingtek Industrial Co., Ltd.			
①	Actuator	UL94 V0	White	LINER		ANGLES		PROJECTION		TITLE			
②	Cover	UL94 V0	Black	.0 ± 0.25		0. ± 2°		BY DSH		BY DSHP SERIES PITCH 1.27mm			
③	Movable	Beryllium Copper	1u"~3u" Gold	.00 ± 0.15		.0 ± 1°		PRODUCT FAMILY DSHP SERIES		PRAT NO. DSHP08TJGET			
④	Terminal	Brass	1u"~2u" Gold	.000± 0.10		.00± 0.5°		DESIGN kathy		FILE NO. DSHP08TJGET-A			
⑤	Base	UL94 V0	Black	DRAWING		CHECK		APPRO.		SIZE A4			
⑥	Terminal Contact	Brass	1u"~3u" Gold	UNIT mm		SCALE 2 : 1		SHEET 1 OF 1		REV. A			
⑦	Mylar	UL94 V0	0.05mm										