

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PBT+30%G.F UL94V-0, 颜色: 黑色.

Housing: PBT+30%G.F UL94V-0, Color: Black

四方针: 青铜, 镍底30u"MIN, 表面镀金1u"MIN

Contact: Bronze, 1u"MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Rating Current: 2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.


温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C

Ordering Information

P220-21 20 A1 A S 145 A 1

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Plating Full of Gold	Semi-gold	INSULATOR MATERIAL	LENGTH OF TERMINAL	PACKING
10: 1.0mm	1~40P	A0=0.8u"	B0=0.8u"	A: PA9T		A: PE Bag
15: 1.5mm		A1=1u"	B1=1u"	B: PA6T		B: Tape & Reel
20: 2.0mm		A2=1.5u"	B2=1.5u"	C: LCP		C: Tube
		A3=2u"	B3=2u"			D: Tube+CAP
		A4=3u"	B4=3u"			E: Tray
		A5=5u"	B5=5u"			
		A6=10u"	B6=10u"			
		A7=15u"	B7=15u"			
		A8=20u"	B8=20u"			
		A9=30u"	B9=30u"			
		S1=Ordinary Tin Plated				
		S2=Matte Tin Plated				
		S3=Tin-plated High-temperature				



RoHS
COMPLIANT

客编:

注意事项

1. 带*为品质重点检验尺寸

				OPERATION		SCALE		Fit	东莞市宇熙精密连接器有限公司			
				X.X	±0.25	UNIT		MM	www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.			
				X.XX	±0.20	SIZE A4		DESIGN	李官森2021.09.14	PART NO	P220-2120A1AS145A1	
				X.XXX	±0.10							
A0	2021.09.14	/	新版发行	Angle	±3°	SHEET 1/1		CHECK		TITLE:	2.0排针 1*20P*2 L=14.5/3.0/3.0 180度 PBT 镀1U金 200个/袋摆整齐	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ. 		APPROVE		Customer No.		