










共面度0.10mm以内



PCB LAYOUT/TOP VIEW
TOLERANCE=± 0.05



说明 (NOTES):

1. 材质 (MATERIAL):

胶芯 (HOUSING): LCP, UL94V-0; COLOR: BLACK
端子 (CONTACT): PHOSPHOR BRONZE
外壳 (SHELL): BRASS

2. 电镀说明 (PLATING):

端子 (CONTACT): SELECTING GOLD $Fu \sim 50u''$ PLATING NICKEL
外壳 (SHELL): PLATING NICKEL

3. 电气性能 (ELECTRICAL):

- 额定电压 (VOLTAGE RATING): 150VACRMS.
- 额定电流 (CURRENT RATING): 1.5A.
- 接触电阻 (CONTACT RESISTANCE): $40m\Omega$ Max.
- 绝缘电阻 (INSULATION RESISTANCE): 500 MEGOHMS MIN @ 500V DC
- 绝缘耐压 (DIELECTRIC WITHSTANDING RESISTANCE): 1000V AC RMS 50Hz. 1MIN.

4. 机械性能 (MECHANICAL):

耐久性 (DURABILITY): 500 Mating Cycles MIN.

5. 环境温度 (ENVIRONMENTAL):

- 存储温度 (STORAGE): -40°C TO 85°C
- 工作温度 (OPERATION): -25°C TO $+85^{\circ}\text{C}$.

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD					
CHECKED:	DATE:	TITLE: RJ45-8P/8C 52E SMT 立贴无柱 全塑 黑色					
DRAWN: L. YUN	DATE: 2018-05-12	PART. NO.	R-RJ45N08P-A007				
		UNIT	mm	SCALE	free		
		FILE NO.	Ckmtw-RJ45-0287	REV.	A	HY04	