

1	2	3	4	5	6	7	8	9	10	11	12	13	14																																																																																										
A												日期	修改者	摘要	版本																																																																																								
B																																																																																																							
C																																																																																																							
D																																																																																																							
E																																																																																																							
F																																																																																																							
G																																																																																																							
H																																																																																																							
I																																																																																																							
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 10%;">F</td> <td>手柄</td> <td>LCP</td> <td>见规格</td> </tr> <tr> <td>E</td> <td>盖板</td> <td>SUS304</td> <td>清洗</td> </tr> <tr> <td>D</td> <td>膜</td> <td>聚酰亚胺</td> <td>黄色</td> </tr> <tr> <td>C</td> <td>弹片</td> <td>SUS301</td> <td>单面镀银</td> </tr> <tr> <td>B</td> <td>基座</td> <td>LCP</td> <td>见规格</td> </tr> <tr> <td>A</td> <td>卡件</td> <td>磷铜</td> <td>镀银</td> </tr> <tr> <td>序号</td> <td>名称</td> <td>材质</td> <td>颜色/镀涂</td> </tr> </table>														F	手柄	LCP	见规格	E	盖板	SUS304	清洗	D	膜	聚酰亚胺	黄色	C	弹片	SUS301	单面镀银	B	基座	LCP	见规格	A	卡件	磷铜	镀银	序号	名称	材质	颜色/镀涂																																																														
F	手柄	LCP	见规格																																																																																																				
E	盖板	SUS304	清洗																																																																																																				
D	膜	聚酰亚胺	黄色																																																																																																				
C	弹片	SUS301	单面镀银																																																																																																				
B	基座	LCP	见规格																																																																																																				
A	卡件	磷铜	镀银																																																																																																				
序号	名称	材质	颜色/镀涂																																																																																																				
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td>8</td> <td>KAN3443-0255C40</td> <td>400 ± 100</td> <td>80 ↑</td> <td>2.5</td> <td>蓝色</td> <td>黑色</td> <td>0.15 ± 0.10</td> <td>3万次以上</td> <td>规格书-003</td> </tr> <tr> <td>7</td> <td>KAN3443-0252C</td> <td>260 ± 50</td> <td>50 ↑</td> <td>2.5</td> <td>红色</td> <td>黑色</td> <td>0.15 ± 0.10</td> <td>10万次以上</td> <td>规格书-003</td> </tr> <tr> <td>6</td> <td>KAN3443-0253B</td> <td>160 ± 50</td> <td>35 ↑</td> <td>2.5</td> <td>白色</td> <td>黑色</td> <td>0.15 ± 0.10</td> <td>10万次以上</td> <td>规格书-003</td> </tr> <tr> <td>5</td> <td>KAN3443-0251D</td> <td>105 ~ 175</td> <td>30 ↑</td> <td>2.5</td> <td>黑色</td> <td>黑色</td> <td>0.15 ± 0.10</td> <td>10万次以上</td> <td>规格书-003</td> </tr> <tr> <td>4</td> <td>KAN3443-0201B</td> <td>160 ± 50</td> <td>35 ↑</td> <td>2.0</td> <td>黑色</td> <td>黑色</td> <td>0.15 ± 0.10</td> <td>10万次以上</td> <td>规格书-003</td> </tr> <tr> <td>3</td> <td>KAN3443-0185C40</td> <td>400 ± 100</td> <td>80 ↑</td> <td>1.8</td> <td>蓝色</td> <td>黑色</td> <td>0.15 ± 0.10</td> <td>3万次以上</td> <td>规格书-003</td> </tr> <tr> <td>2</td> <td>KAN3443-0182C</td> <td>260 ± 50</td> <td>50 ↑</td> <td>1.8</td> <td>红色</td> <td>黑色</td> <td>0.15 ± 0.10</td> <td>10万次以上</td> <td>规格书-003</td> </tr> <tr> <td>1</td> <td>KAN3443-0181D</td> <td>105 ~ 175</td> <td>30 ↑</td> <td>1.8</td> <td>黑色</td> <td>黑色</td> <td>0.15 ± 0.10</td> <td>10万次以上</td> <td>规格书-003</td> </tr> <tr> <td>序号</td> <td>型号</td> <td>克力(g)</td> <td>回力(g)</td> <td>"H"(mm)</td> <td>手柄色</td> <td>底座色</td> <td>行程(mm)</td> <td>寿命</td> <td>服从规格</td> </tr> </table>														8	KAN3443-0255C40	400 ± 100	80 ↑	2.5	蓝色	黑色	0.15 ± 0.10	3万次以上	规格书-003	7	KAN3443-0252C	260 ± 50	50 ↑	2.5	红色	黑色	0.15 ± 0.10	10万次以上	规格书-003	6	KAN3443-0253B	160 ± 50	35 ↑	2.5	白色	黑色	0.15 ± 0.10	10万次以上	规格书-003	5	KAN3443-0251D	105 ~ 175	30 ↑	2.5	黑色	黑色	0.15 ± 0.10	10万次以上	规格书-003	4	KAN3443-0201B	160 ± 50	35 ↑	2.0	黑色	黑色	0.15 ± 0.10	10万次以上	规格书-003	3	KAN3443-0185C40	400 ± 100	80 ↑	1.8	蓝色	黑色	0.15 ± 0.10	3万次以上	规格书-003	2	KAN3443-0182C	260 ± 50	50 ↑	1.8	红色	黑色	0.15 ± 0.10	10万次以上	规格书-003	1	KAN3443-0181D	105 ~ 175	30 ↑	1.8	黑色	黑色	0.15 ± 0.10	10万次以上	规格书-003	序号	型号	克力(g)	回力(g)	"H"(mm)	手柄色	底座色	行程(mm)	寿命	服从规格
8	KAN3443-0255C40	400 ± 100	80 ↑	2.5	蓝色	黑色	0.15 ± 0.10	3万次以上	规格书-003																																																																																														
7	KAN3443-0252C	260 ± 50	50 ↑	2.5	红色	黑色	0.15 ± 0.10	10万次以上	规格书-003																																																																																														
6	KAN3443-0253B	160 ± 50	35 ↑	2.5	白色	黑色	0.15 ± 0.10	10万次以上	规格书-003																																																																																														
5	KAN3443-0251D	105 ~ 175	30 ↑	2.5	黑色	黑色	0.15 ± 0.10	10万次以上	规格书-003																																																																																														
4	KAN3443-0201B	160 ± 50	35 ↑	2.0	黑色	黑色	0.15 ± 0.10	10万次以上	规格书-003																																																																																														
3	KAN3443-0185C40	400 ± 100	80 ↑	1.8	蓝色	黑色	0.15 ± 0.10	3万次以上	规格书-003																																																																																														
2	KAN3443-0182C	260 ± 50	50 ↑	1.8	红色	黑色	0.15 ± 0.10	10万次以上	规格书-003																																																																																														
1	KAN3443-0181D	105 ~ 175	30 ↑	1.8	黑色	黑色	0.15 ± 0.10	10万次以上	规格书-003																																																																																														
序号	型号	克力(g)	回力(g)	"H"(mm)	手柄色	底座色	行程(mm)	寿命	服从规格																																																																																														
绘图 (DRAW)		未标注公差尺寸 METRIC TOLERANCE		型号: (DRAWING NO)		TS-1185-W-4P-H2.0-160		品名: (TITLE)		3*4四脚圆盖开关				浙江创都电子科技有限公司																																																																																									
校对 (CHECK)		.0 ± 0.30 .00 ± 0.20 .000 ± 0.10		图档: (DWG ID)		成品图		时间: TIME		2021.09.19		页次 (PAGE)	1/1																																																																																										
核准 (APPR)				投影法: (PROJECT)		材 质: (MATERIAL)		比 例: (SCALE)	FIT	单 位: (NUITS)	mm	版 本: (REV)	A0																																																																																										