








序号 No.	品名Name	材质Material
①	1.0拔波3代滤芯(H2.0) Housing (H=2.0) 1.0 Pitch ZIF Type 3	LCP UL94V-0 本色 Natural
②	1.0拔波上接端子(H2.0) 1.0Pitch H2.0 ZIF Type terminal	铜合金/表面镀锡 Copper Alloy/ Tin Plating
③	1.0拔波3代后盖(H2.0) Actuator (H=2.0) 1.0 Pitch ZIF Type 3	LCP UL94V-0 黑色 Black
④	1.0拔波3代焊片(H2.0) 1.0 Pitch ZIF Type 3 fitting Nail (H=2.0)	铜合金/表面镀锡 Copper Alloy/ Tin Plating



- Technical Index:
1. The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.
 2. Temperature range: -25° C~85° C.
 3. Rated voltage: 50V, AC/DC.
 4. Contact resistance: ≤0.03Ω.
 5. Insulation resistance: ≥500MΩ.

适用扁平线 (Applicable Flat Cable)

CKT	DIM A	DIM B	DIM C	DIM D
4	3.00	5.06	10.10	
5	4.00	6.06	11.10	
6	5.00	7.06	12.10	
7	6.00	8.06	13.10	
8	7.00	9.06	14.10	
9	8.00	10.06	15.10	
10	9.00	11.06	16.10	5.20
11	10.00	12.06	17.10	
12	11.00	13.06	18.10	
13	12.00	14.06	19.10	
14	13.00	15.06	20.10	
15	14.00	16.06	21.10	
16	15.00	17.06	22.10	
17	16.00	18.06	23.10	
18	17.00	19.06	24.10	
19	18.00	20.06	25.10	
20	19.00	21.06	26.10	
21	20.00	22.06	27.10	
22	21.00	23.06	28.10	
23	22.00	24.06	29.10	5.75
24	23.00	25.06	30.10	
25	24.00	26.06	31.10	
26	25.00	27.06	32.10	
27	26.00	28.06	33.10	
28	27.00	29.06	34.10	
29	28.00	30.06	35.10	
30	29.00	31.06	36.10	

适用线路板 (PCB LAYOUT)									
				APPROVALS		DATE		DEALON 德之隆® ELECTRONICS CO.,LTD TITLE: 0.5 Pitch ZIF R/A Top Type CONN. (H=2.0) PART NO. FC10-SXXDCU-00 SCALE: 1:1 SHEET 1 OF 1	
DRAWN		G.M.Chen		2025/6/18					
CHECKED									
APPROVALS									
TOLERANCES ARE		30~以上 ±0.30 10~30 ±0.20 5~10 ±0.15 ~5 ±0.10		ANGLE ±2°					
UNIT: mm		SCALE: 1:1		SHEET 1 OF 1					
DRAWING NO.				PROJ. ④					
ECN NO.		REV.		DATE.		DESCRIPTION.		CHANGE.	
A						NEW			