








序号 No.	品名 Name	材质 Material
①	1. 0拉拔3代滤芯 (H2. 0) 1. 0 Pitch ZIF Type 3 Housing (H2= 0)	LCP UL94V-0 本色 Natural
②	1. 0拉拔下接端子 (H2. 0) 1. 0 Pitch L2 ZIF R/A Type Under terminal	铜合金/表面镀锡 Copper Alloy/ Tin Plating
③	1. 0拉拔3代后盖 (H2. 0) 1. 0 Pitch ZIF Type 3 Actuator (H2= 0)	LCP UL94V-0 黑色 Black
④	1. 0拉拔3代弹片 (H2. 0) 1. 0 Pitch ZIF Type 3 Fitting Nail (H2= 0)	铜合金/表面镀锡 Copper Alloy/ Tin Plating



适用扁平线(Applicable Flat Cable)



Technical Index:

1. The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.
2. Temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. Rated voltage: 50V, AC/DC.
4. Contact resistance: $\leq 0.03\Omega$.
5. Insulation resistance: $\geq 500\text{M}\Omega$

CKT	DIM A	DIM B	DIM C	DIM E
4	3.00	5.06	10.10	5.20
5	4.00	6.06	11.10	
6	5.00	7.06	12.10	
7	6.00	8.06	13.10	
8	7.00	9.06	14.10	
9	8.00	10.06	15.10	
10	9.00	11.06	16.10	
11	10.00	12.06	17.10	
12	11.00	13.06	18.10	
13	12.00	14.06	19.10	
14	13.00	15.06	20.10	5.75
15	14.00	16.06	21.10	
16	15.00	17.06	22.10	
17	16.00	18.06	23.10	
18	17.00	19.06	24.10	
19	18.00	20.06	25.10	
20	19.00	21.06	26.10	
21	20.00	22.06	27.10	
22	21.00	23.06	28.10	
23	22.00	24.06	29.10	
24	23.00	25.06	30.10	
25	24.00	26.06	31.10	
26	25.00	27.06	32.10	
27	26.00	28.06	33.10	
28	27.00	29.06	34.10	
29	28.00	30.06	35.10	
30	29.00	31.06	36.10	

适用线路板 (PCB LAYOUT)									
						APPROVALS		DATE	
						DRAWN	G.M.Chen	2025/6/18	
						CHECKED			
						APPROVALS			
	A		NEW					PART NO.	FC10-SXXDCT-00
								UNIT: mm	SCALE: 1:1
								DRAWING NO.	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE		
							30~MAX ±0.30 ANGLE		
							10~30 ±0.20		
							5~10 ±0.15	±2°	
							~5 ±0.10		
								DRAWING NO.	
								PROJ.	SHEET 1 OF 1