



Technical Index:

1. The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage defects, cracks and other phenomena.
2. Temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. Rated voltage: 50V, AC/DC.
4. Contact resistance: $\leq 0.03\Omega$.
5. Insulation resistance: $\geq 500M\Omega$

序号 (NO.)	品名 (Name)	材质 (Material)
①	1.0欧盖胶盖 (H=2.0) 1.0 Pitch Easy-on Type Housing (H=2.0) 1.0欧盖端子 (H=2.0) 1.0 Pitch Easy-on Type Terminal (H=2.0)	LCF U9490 本色 Natural
②	1.0欧盖后盖 (H=2.0) 1.0 Pitch Easy-on Type Actuator (H=2.0)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
③	1.0欧盖后盖 (H=2.0) 1.0 Pitch Easy-on Type Actuator (H=2.0)	LCF U9490 黑色 Black
④	1.0欧盖垫片 (H=2.0) 1.0 Pitch Easy-on Type Fitting Pad (H=2.0)	铜合金/表面镀锡 Copper Alloy/ Tin Plating

	DIMA±0.05					
通用线路板 (PCB LAYOUT)						
	A		NEW			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
				APPROVALS DRAWN G.M.Chen 2025/6/18		
				CHECKED		
				TOLERANCES ARE 30~90° ±0.30 10~30 ±0.20 5~10 ±0.15 ~5 ±0.10 ANGLE ±2'		
				PART NO. FC10-SXXCT-00		
				UNIT: mm SCALE: 1:1		
				SHEET 1 OF 1		
				DRAWING NO. PROD. ⑤		
				TITLE: FPC CONNECTOR		
				DEALON 德之隆® ELECTRONICS CO.,LTD		