


P.C. Board Layout

Material:

Housing: PA66+30%GF, UL94V-0.

Contacts: Brass, Gold Plated on Contact Area and 100u" Tin Plated on Solder Tail over Nickel 50u".

Electrical Characteristics:

Voltage Rating: 250V.

Current Rating: 1 AMP.

Dielectric Withstanding Voltage: AC 500V.

Insulator Resistance: 1000MΩ min.

Contact Resistance: 30mΩ max.

Operating Temperature: -55°C~+105°C.

***RoHS Compliant**

8206-
Series

120
Position

N
N: Internal Code

P
P: With Post

A
A: Tray Package

Tolerances	Dwg. No.	8206D02001		Title: 8206 Series PCI 120P Connector		深圳市格林柏电子技术开发有限公司			
x = ±0.30 .x = ±0.30 .xx = ±0.20 .xxx = ±0.05	Projection					P/N: 8206-120NPA			
	Unit	mm	Scale	1:N					
	Drawn By	Martin 12/02'21		Φ720	SHEET 1/1 Ver.No. B5				