




### 材料及电镀

①. 塑件主体: PA66, UL94V-0

②. 焊 针: 黄铜, 镀镍

### 电气性能

额定电压: 300V

额定电流: 15A

接触电阻: 20mΩ (Max)

绝缘电阻: 500MΩ \DC500V

耐 电 压: AC2000V\1Min

### 机械性能

温度范围: -40℃ ~ +105℃

瞬时温度: +250℃ , 5秒

### Ordering Information

HC2EDG \* \* - \* - NP - \*

|      |          |             |             |          |
|------|----------|-------------|-------------|----------|
| Type | Pin 1 插针 | PITCH       | No. of Pins | Colour   |
|      | Pin 2 插针 | 2.54=2.54mm | 2-24Pin     | Y=Green  |
|      | Pin 3 插针 | 3.5=3.50mm  | 2P=2Pin     | L=Blue   |
|      | Pin 4 插针 | 3.81=3.81mm | 3P=3Pin     | O=Orange |
|      | Pin 5 插针 | 5.08=5.08mm | .....       | R=Red    |
|      |          | 7.62=7.62mm |             | B=Black  |
|      |          |             |             | GR=Gray  |

|           |                        |                    |                   |        |                   |                                                                                       |  |  |                           |                                                                                                                                                                    |     |  |
|-----------|------------------------|--------------------|-------------------|--------|-------------------|---------------------------------------------------------------------------------------|--|--|---------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|--|
|           |                        |                    | GENERAL TOLERANCE |        | 制 图<br>DRAWING    | 07                                                                                    |  |  |                           | <div> 深圳市华灿天禄电子有限公司</div> <div>ShenzhenhuacantianluELECTRONICS CO., LTD</div> |     |  |
|           |                        |                    | DIM               | TOL    | 审 核<br>CHECK      |                                                                                       |  |  |                           |                                                                                                                                                                    |     |  |
|           |                        |                    | X. X              | ± 0.50 | 批 准<br>APPROVAL   | 产品名称<br>TITLE                                                                         |  |  | 5.08 单排 插拔式 接线端子<br>封闭 直针 | 版 本<br>REV.                                                                                                                                                        | A   |  |
| 1         | 初版发行                   |                    | X. XX             | ± 0.30 |                   | 产品料号<br>PART NO.                                                                      |  |  | HC2EDGVC-5.08-NP-X        | 单 位<br>UNITS                                                                                                                                                       | mm  |  |
| 序号<br>No. | 变更内容<br>MODIFY CONTENT | 日 期<br>MODIFY DATE | Angle             | ± 3.0° | 投 影<br>Projection |  |  |  | 材 料<br>MATERIAL           | 页 次<br>SHEET                                                                                                                                                       | 1/1 |  |