





Tape width 16 and 24 mm





Tape width 32 and 44 mm



NOTE:

- 1.10 Sprocket hole pitch cumulative tolerance  $\pm 0.20$ .
2. Carrier camber is within 1mm in 100mm.
3. Material: black conductive polystyrene alloy.
4. Material Thickness:  $0.3 \pm 0.05$ mm.
5. All dimensions meet EIA-481-B requirements.
6. 5000pcs Pef Reel.
7. For tape width(dim W)16 and 24mm pilot holes are provided on one sides.  
For tape width(dim W)32, 44 and 56mm pilot holes are provided on both sides.



| PIN NO.     | W  | C    | PCS /REEL | REEL/CARTON | SUM(PCS) |
|-------------|----|------|-----------|-------------|----------|
| 4PIN~20PIN  | 16 | —    | 1000      | 12          | 12000    |
| 21PIN~40PIN | 24 | —    | 1000      | 10          | 10000    |
| 41Pin~50PIN | 32 | 28.4 | 1000      | 8           | 8000     |
| 51Pin~60PIN | 44 | 40.4 | 1000      | 6           | 6000     |

|           |                        |                   |                  |            |                   |                                                           |                                         |              |     |
|-----------|------------------------|-------------------|------------------|------------|-------------------|-----------------------------------------------------------|-----------------------------------------|--------------|-----|
|           |                        |                   | GENEAL TOLERANCE |            | 制 图<br>DRAWING    | 深圳市华灿天禄电子有限公司<br>ShenzhenhuacantianlueELECTRONICS CO.,LTD |                                         |              |     |
|           |                        |                   | DIM              | TOL        | 审 核<br>CHECK      |                                                           |                                         |              |     |
|           |                        |                   | X. X             | $\pm 0.30$ | 批 准<br>APPROVAL   | 产品名称<br>TITLE                                             | BTB 0.8 单槽 母座 立式侧插<br>座高5.1mm 编带 带柱-包装图 | 版 本<br>REV.  | A   |
|           |                        |                   | X. XX            | $\pm 0.20$ | 比 例<br>SCALE      | 产品料号<br>PART NO.                                          | IHC-PBB08-1-N-F-S-H5. 1-XX-R-P-06       | 单 位<br>UNITS | mm  |
|           |                        |                   | X. XXX           | $\pm 0.10$ | 投 影<br>Projection | 材 料<br>MATERIAL                                           |                                         | 页 次<br>SHEET | 2/2 |
| 1         | 初版发行                   |                   |                  |            |                   |                                                           |                                         |              |     |
| 序号<br>No. | 变更内容<br>MODIFY CONTENT | 日期<br>MODIFY DATE |                  |            |                   |                                                           |                                         |              |     |