





公差参数:

Pin	Dim P	Dim L
2-6P	±0.10	±0.20
7-12P	±0.20	±0.30
13-18P	±0.25	±0.40
19-24P	±0.30	±0.50



材料及电镀

①. 塑件主体: PA66, UL94V-0

②. 焊 针: 黄铜, 镀镍

电气性能

额定电压: 300V

额定电流: 15A

接触电阻: 20mΩ (Max)

绝缘电阻: 500MΩ \DC500V

耐 电 压: AC2000V\1Min

机械性能

温度范围: -40℃ ~ +105℃

瞬时温度: +250℃ , 5秒

Ordering Information

HC2EDG	*	*	*	-	NP	-	*
Type		Pin	PITCH		No. of Pins		Colour
1.0mm	1.0mm	2.54=2.54mm	2.54=2.54mm	2-24Pin			Y=Green
1.27mm	1.27mm	3.5=3.5mm	3.5=3.5mm	2-24Pin			L=Blue
1.5mm	1.5mm	3.81=3.81mm	3.81=3.81mm	2P=2Pin			O=Orange
		5.08=5.08mm	5.08=5.08mm	3P=3Pin			R=Red
		7.62=7.62mm	7.62=7.62mm				B=Black
							GR=Gray

			GENREL TOLERANCE		制 图 DRAWING	07				 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD		
			DIM TOL		审 核 CHECK							
			X.X	± 0.50	批 准 APPROVAL	产品名称 TITLE		5.08 单排 插拔式 接线端子 封闭 弯针		版 本 REV.	A	
1	初版发行		X.XX	± 0.30	比 例 SCALE	产品料号 PART NO.		HC2EDGRC-5.08-NP-X		单 位 UNITS	mm	
序号 No.	变更内容 MODIFY CONTENT		X.XXX	± 0.10	投 影 Projection	材 料 MATERIAL				页 次 SHEET	1/1	
		日 期 MODIFY DATE	Angle	± 3.0°								