









修 订	标 记	修 改 描 要	签 名	日 期
REV	AO	NEW DWG		2016-03-12

NOTES:

- HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0
- ACTUATOR: LCP HIGH-TEMP THERMOPLASTIC UL94V-0
- TERMINAL:PHOSPHOR BRONZE
PLATING:1*''GOLD FLASH OR 100~150*''TIN(LEAD FREE)
OVERALL 50~100*''NICKEL UNDER PLATED.
- FITTING NAIL:PHOSPHOR BRONZE
PLATING:100~150*''TIN(LEAD FREE)
OVERALL 50~100*''NICKEL UNDER PLATED.
- SPECIFICATION:
CURRENT RATING: 0.5A 50V AC/DC
CONTACT RESISTANCE: 30mΩ MAX
INSULATION RESISTANCE: 100MΩ AT 500V DC
OPERATING TEMPERATURE RANGE: -40°C~85°C
WITHSTANDING VOLTANG: 500V AC/minute

NO.of contacts	Dimensions				NO.of contacts	Dimensions			
	A.	B.	C.	D.		A.	B.	C.	D.
40	24.90	19.50	21.90	25.20	69	39.40	34.00	36.40	39.70
41	25.40	20.00	22.40	25.70	70	39.90	34.50	36.90	40.20
42	25.90	20.50	22.90	26.20	71	40.40	35.00	37.40	40.70
43	26.40	21.00	23.40	26.70	72	40.90	35.50	37.90	41.20
44	26.90	21.50	23.90	27.20	73	41.40	36.00	38.40	41.70
45	27.40	22.00	24.40	27.70	74	41.90	36.50	38.90	42.20
46	27.90	22.50	24.90	28.20	75	42.40	37.00	39.40	42.70
47	28.40	23.00	25.40	28.70	76	42.90	37.50	39.90	43.20
48	28.90	23.50	25.90	29.20	77	43.40	38.00	40.40	43.70
49	29.40	24.00	26.40	29.70	78	43.90	38.50	40.90	44.20
50	29.90	24.50	26.90	30.20	79	44.40	39.00	41.40	44.70
51	30.40	25.00	27.40	30.70	80	44.90	39.50	41.90	45.20
52	30.90	25.50	27.90	31.20	81	45.40	40.00	42.40	45.70
53	31.40	26.00	28.40	31.70	82	45.90	40.50	42.90	46.20
54	31.90	26.50	28.90	32.20	83	46.40	41.00	43.40	46.70
55	32.40	27.00	29.40	32.70	84	46.90	41.50	43.90	47.20
56	32.90	27.50	29.90	33.20	85	47.40	42.00	44.40	47.70
57	33.40	28.00	30.40	33.70	86	47.90	42.50	44.90	48.20
58	33.90	28.50	30.90	34.20	87	48.40	43.00	45.40	48.70
59	34.40	29.00	31.40	34.70	88	48.90	43.50	45.90	49.20
60	34.90	29.50	31.90	35.20	89	49.40	44.00	46.40	49.70
61	35.40	30.00	32.40	35.70	90	49.90	44.50	46.90	50.20
62	35.90	30.50	32.90	36.20	91	50.40	45.00	47.40	50.70
63	36.40	31.00	33.40	36.70	92	50.90	45.50	47.90	51.20
64	36.90	31.50	33.90	37.20	93	51.40	46.00	48.40	51.70
65	37.40	32.00	34.40	37.70	94	51.90	46.50	48.90	52.20
66	37.90	32.50	34.90	38.20	95	52.40	47.00	49.40	52.70
67	38.40	33.00	35.40	38.70	96	52.90	47.50	49.90	53.20
68	38.90	33.50	35.90	39.20	97	53.40	48.00	50.40	53.70



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co., LTD
电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: FPC0.5间距2.2高掀盖式带扣A款	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDGC0527A-xxCL-GF
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	SCALE
			UNIT
			CODE NUMBER
		2016-03-12	1:1
			mm
			A001

A

B


C

D


E

F

修订	标记	修改摘要	签名	日期
REV	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
AO		NEW DWG		2016-03-12




APPLICABLE FPC/FFC



APPLICABLE FPC/FFC

一体补强板铝箔FFC线



一体补强板铝箔FFC线

NO.of contacts	Dimensions		NO.of contacts	Dimensions	
	B.	E.		B.	E.
40	19.50	21.85	69	34.00	36.35
41	20.00	22.35	70	34.50	36.85
42	20.50	22.85	71	35.00	37.35
43	21.00	23.35	72	35.50	37.85
44	21.50	23.85	73	36.00	38.35
45	22.00	24.35	74	36.50	38.85
46	22.50	24.85	75	37.00	39.35
47	23.00	25.35	76	37.50	39.85
48	23.50	25.85	77	38.00	40.35
49	24.00	26.35	78	38.50	40.85
50	24.50	26.85	79	39.00	41.35
51	25.00	27.35	80	39.50	41.85
52	25.50	27.85	81	40.00	42.35
53	26.00	28.35	82	40.50	42.85
54	26.50	28.85	83	41.00	43.35
55	27.00	29.35	84	41.50	43.85
56	27.50	29.85	85	42.00	44.35
57	28.00	30.35	86	42.50	44.85
58	28.50	30.85	87	43.00	45.35
59	29.00	31.35	88	43.50	45.85
60	29.50	31.85	89	44.00	46.35
61	30.00	32.35	90	44.50	46.85
62	30.50	32.85	91	45.00	47.35
63	31.00	33.35	92	45.50	47.85
64	31.50	33.85	93	46.00	48.35
65	32.00	34.35	94	46.50	48.85
66	32.50	34.85	95	47.00	49.35
67	33.00	35.35	96	47.50	49.85
68	33.50	35.85	97	48.00	50.35



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表TITLE:
产品名称: FPC0.5间距2.2高掀盖式带扣A款

X.X ±0.30 X.X* ±3°

APPD:
核准:PART NO:
产品编号: HDGC0527A-xxCL-GF

X.XX ±0.20 X.XX* ±2°

CHECK: 王建业







DATE SCALE UNIT CODE NUMBER

X.XXX ±0.10 X.XXX* ±1°

DRAW: 黄艳兰
绘图:

2016-03-12 1:1 mm A001

修 订	标 记	修 改 描 要	签 名	日 期
REV NO	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
		NEW DWG		2016-03-12



- NOTES:
- 1.Component load per 13" reel:2000 pcs
 - 2.Material: white conductive polystyrene alloy.
 - 3.Thickness:0.4±0.05mm
 - 4.All dimensions meet EIA-481-C requirements

No.of Contacts	DIM			REEL (CARTON)	SUM(PCS)
	A	B	C		
40pin~57pin	44	20.2	40.4	6	12000
58pin~81pin	44	52.4	26.2	5	10000
82pin~96pin	72	68.4	34.2	4	8000



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				 		TITLE: 产品名称: FPC0.5间距2.2高掀盖式带扣A款			
X.X	±0.30	X.X*	±3°	APPD: 核准:	PART NO: 产品编号: HDGC0527A-xxCL-GF				
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER	
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001	