






修 订		标 记	修 改 描 要	签 名	日 期
REV	NO		REVISION DESCRIPTION	SIGNATURE	DATE
			NEW DWG		2016-03-12



RECOMMENDED P.C.BOARD LAYOUT

- NOTES:
- 1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0
 - 2.TERMINAL:PHOSPHOR BRONZE
PLATING:1μ" GOLD FLASH OVERALL 50~100μ" NICKEL UNDER PLATED.
 - 3.VOLTAGE:100VAC
 - 4.CURRENT RATING: 0.5 A
 - 5.INSULATION RESISTANCE: 500MΩ
 - 6.DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC
 - 7.CONNECTOR MATING FORCE:90GF MAX.
 - 8.TEMPERATURE RATING:-40℃ TO+125℃
- COLOR:BEIGE



NO.of contacts	Dimensions			
	A.	B.	C.	D.
40	21.80	15.20	16.80	20.20
60	29.80	23.20	24.80	28.20
80	37.80	31.20	32.80	36.20
100	45.80	39.20	40.80	44.20
120	53.80	47.20	48.80	52.20
140	61.80	55.20	56.80	60.20
160	69.80	63.20	64.80	68.20
180	77.80	71.20	72.80	76.20
200	85.80	79.20	80.80	84.20



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: BTB0.8mm单槽AMP公座合高5.0			
X.X ±0.30	X.X° ±3°	APPD: 核准:		PART NO: 产品编号: HDGC0812M-BTB-nP			
X.XX ±0.20	X.XX° ±2°	CHECK: 校对: 王建业		DATE	SCALE	UNIT	CODE NUMBER
X.XXX ±0.10	X.XXX° ±1°	DRAW: 绘图: 黄艳兰		2016-03-12	1:1	mm	A001