





Rev No.	Description of Revision	Date	Name	Approved	ECN No.




Specifications:

1. Rated Voltage : 125V AC/DC
2. Rated Current : 2A AC,DC
3. Withstand Voltage : 200V AC/minute
4. Contact Resistance: 50mΩ (MAX.)
5. Insulation Resistance: 100mΩ (MIN.)
6. Storage Temperature Range: -40°C~+85°C;
7. Operation Temperature Range: -25°C~+70°C;



RECOMMENDED P.C.B LAYOUT TOP VIEW
(GENERAL TOLERANCE ±0.10)



PIN数	MID. A	MID. B	MID. C
2P	2.00	8.00	2.00
3P	4.00	10.00	4.00
4P	6.00	12.00	6.00
5P	8.00	14.00	8.00
6P	10.00	16.00	10.00

③	端子	黄铜H65	镀亮锡	6PCS
②	固定片	黄铜H65	镀亮锡	2PCS
①	塑胶主体	LCP	本色	1PCS
序号	配件名称	材质	电镀/颜色	数量

UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE HX-PH2.0-2ALB wire-to-board header	
DECIMALS:	ANGLES	Drwng:	黄彬
X. ±0.15	X. ±2°	PART NO.	WF004-LT20006-01
X.X ±0.10	X.X* ±1°	Checked:	张伟
X.XX ±0.05	X.XX* ±0.5°	Approved:	罗小春
X.XXX ±0.03		SIZE:	A4
		SHEET:	1 OF 1
		REV.:	A
CUSTOMER COPY			

®
韩下 HANXIA 深圳市韩下电子有限公司



深圳市韩下电子有限公司
Shenzhen Hanxia Electronic Co., Ltd
Tel: 0755-23086569 Email: shouhan2@so-han.com

承 认 书

SPECIFICATION FOR APPROVAL

产品编码

Material code:

产品名称 Project:

针座

规格型号 Part No:

HX-PH2.0-2ALB wire-to-board header

贵公司承认印 Approval signatures

料号/Part No.	签章/Signatures

日期 Date:

拟制/Drawn	黄彬	
审核/Check	张伟	
批准/Approved	罗小春	