








修 订		标 记	修 改 描 要	签 名	日 期
REV		MARK	REVISION DESCRIPTION	SIGNATURE	DATE
A0			NEW DWG		2016-03-12




PCB LAYOUT
TOLERANCE : ±0.05

1.MATERIAL
HOUSING:LCP UL 94V-0
ACTUATOR:LCP UL 94V-0
CONTACTS: PHOSPHOR BRONZE
PEG: PHOSPHOR BRONZE
2.PLATING:
CONTACTS:1μ" GOLD FLASH
OVERALL 50~100μ" NICKEL UNDER PLATED.
PEG:100~150μ" TIN(LEAD FREE)
OVERALL 50~100μ" NICKEL UNDER PLATED.
3.PERFORMANCE CHARACTERISTICS:
OPERATING VOLTAGE:50V AC,DC
CURRENT RATING:0.5A AC,DC
OPERATING TEMPERATURE:-25°C~+85°C

No. of Contacts	DIM.			
	A	B	C	D
06	7.30	2.50	3.60	5.72
08	8.30	3.50	4.60	6.72
09	8.80	4.00	5.10	7.22
10	9.30	4.50	5.60	7.72
12	10.30	5.50	6.60	8.72
13	10.80	6.00	7.10	9.22
15	11.80	7.00	8.10	10.22
16	12.30	7.50	8.60	10.72
18	13.30	8.50	9.60	11.72
24	16.30	11.50	12.60	14.72
28	18.30	13.50	14.60	16.72
30	19.30	14.50	15.60	17.72
32	20.30	15.50	16.60	18.72
40	24.30	19.50	20.60	22.72
49	28.80	24.00	25.10	27.22
50	29.30	24.50	25.60	27.72
57	32.80	28.00	29.10	31.22
60	34.30	29.50	30.60	32.72

RECOMMENDED FPC DIMENSION





深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co., LTD
电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: FPC0.5间距1.75高掀盖下接带扣				
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDGC05175-xxCL-GF			
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001