

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance: 20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance: 1000M Ω Min

Operation Temperature: -40°C to $+105^{\circ}\text{C}$

Contact Material:Brass



Contact Plating: Au Or Tin Over Ni

Insulator Material: Polyester (UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30–60 seconds

(260°C for 10 seconds)





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)

[illegible]

Dimension antitheses list								
ITEM	PA	PB	PC	L1	L2	L3	H	W
001	6.00	4.30	3.00	13.80			2.5	2.5
Alternate								

Ordering Information



深圳市连盛精密连接器有限公司										
						OPERATION		DRAW		
						X.X	±0.30			
						X.XX	±0.20			
						X.XXX	±0.10			
						Angle	±3°	CHECK		
						DIM	TOL			
AO	2012.07.02		NEW DRAWING					APPROVE		
REV	DATE		MODIFICATION DESCRIPTION		CHANGE					
		SCALE	FIT							
		UNIT	mm							
		SIZE	A4							
		SHEET	1/1							
		PROJ.								
PART NO.			1010301716							
TITLE:			2.54PH 1XNP 90度							

深圳市连盛精密连接器有限公司

PART NO.	1010301716
----------	------------

TITLE:	2.54PH 1XNP 90度
--------	-----------------