





SCHEMATIC

PCB LAYOUT
TOP VIEW

PIN	Ø2.0	Ø2.5	
APPD.			

				TOLERANCE UNLESS SPECIFIED							
6	COVER	PBT				UP TO 5mm: ±0.1	ANGULAR	1	2017.3.8	增加重量尺寸	
5	CONTACT FOOT	BRASS	1	Sn-PLATED	ABOVE 5mm: ±0.2	±1°		NO	DATE	REVISIONS	BY APPD
4	PIN	BRASS	1	Ni-PLATED	TITLE: DC JACK			UNIT : MM		ROHS	DWN
3	SPRING	STEEL/PBS	1	Sn-PLATED	MODEL: DC-016-2.0-PU (HY)			SCALE: 1:1		COMPLIANT	CHK'D
2	FLAT PIECE	BRASS	1	Sn-PLATED	 HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司					APPD	
1	HOUSING	PBT	1								
NO.	PART	NAME	MATERIAL	QTY	FINISHING				PRO.AGL: 		REV :A1