





SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:−40°C to +105°C

Contact Material:Brass
Contact Plating:Au Or Tin Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30–60 seconds
(260°C for 10 seconds)



Ordering Information

P X X X XX X XX X XXX

产品型号	间距	塑胶材质	接触	绝缘材料	产品序号	电绝缘度	包装方式	序列号
P=排针	1=1.27 A=1.0	1=单排	1~40P	1=DIP	1=FRIT	00=常规	1=管接	
	2=2.0 B=1.5	2=双排		2=RA	2=LCP	01=1u"	2=通接	
	3=2.54 C=2.0	3=三排		3=SMT	3=PPS	02=2u"	3=叠接	
	5=1.9 D=2.5	4=四排		4=SMT	4=PA46	03=3u"	4=叠接	
	A=1.27*2.54			5=微焊脚	5=PA6T		5=叠接	
				9=PA9T				

Dimension antitheses list									
ITEM	PA	PB	PW	L1	L2	L3	H	W	
001	6.00	3.20	5.00	11.00			2.5	2.5	
Alternate									

深圳市连盛精密连接器有限公司											
PART NO.		1010301749									
TITLE:		2.54PH 1XNP SMT									
REV	DATE	MODIFICATION DESCRIPTION		CHANGE		OPERATION		SCALE		FIT	
						DRAW					
						X.X	±0.30		UNIT	mm	
						X.XX	±0.20	CHECK	SIZE	A4	
A0	2012.03.28	NEW DRAWING				X.XXX	±0.10		SHEET	1/1	
						Angle	±3°	APPROVE			
						DIM	TOL		PROJ.		